viledon®

MVP CASSETTE FILTERS – QUALITY WITH AN OPTIMUM PRICE-PERFORMANCE RATIO

FOR OPERATION OF VENTILATION SYSTEMS

FILTERTYPE	FILTER CLASS TO ISO 16890	FILTER CLASS TO EN 779:2012	ENERGY EFFICIENCY CLASS*
MVP 75	ISO ePM10 75%	M 6	_
MVP 85	ISO ePM2,5 70%	F7	В
MVP 95	ISO ePM1 70%	F8	А
MVP 98	ISO ePM1 85%	F9	В











The application

Viledon® MVP cassette filters are used in supply, exhaust and recirculated-air filtration for ventilation systems, such as those in

- office buildings
- factory/production halls
- airports, libraries, museums
- laboratories, hospitals
- old people's homes and care facilities, etc.

The characteristics

- Micro-glassfiber papers are used as filter media.
- The filter frame consists of halogenfree plastics.
- The dimensionally stable media pleat packs are casted into the plastic frame providing excellent functional safety against dust penetration during operation.

- MVP filters are constructed for simple and safe handling at installation.
- Viledon® MVP filters are microbiologically inactiv and meet all the criteria of VDI Guideline 6022 "Hygiene Requirements for HVAC systems and units".
- The entire filter element is free of metals and halogenes, corrosion-free, fully incinerable and thereby disposal-friendly.

The special features

- MVP cassette filters excel in terms of low pressure drop and offer an optimum price-performance ratio.
- MVP 95 cassette filters reach energy efficiency class A according to EURO-VENT ensuring reduced energy costs and reduced CO₂ emissions.

- The frame offers various possibilities for the installation of clips to hold prefilters.
- Patented Viledon® modular clip-on system with optionally installed pins for combination with other pre- or final filters for a 2-in-1 system solution.
- MVP cassette filters are available with six instead of eight pleat panels and with polyurethane-foamed gasket on the up- or downstream side.


GEOMETRIES AVAILABLE		1/1	5/6	1/2
Nominal volume flow rate	m³/h	4,250	3,500	2,000
Filtering area	m²	18	14.5	8.5
Front frame for mounting frame	mm	592×592×25 610×610	490×592×25 508×610	287×592×25 305×610
Overall depth	mm		292	
Weight, approx.	kg	5.5	4.5	3.2
Temperature-resistance	°C		70	
Moisture-resistance (rel. hum.)	%		100	



TECHNICAL FILTER TEST DATA TO EN 779 AND ISO 16890


Fractional collection efficiency curves

MVP98



- MVP95

Initial pressure drop curves



Nominal volume flow rate

MVP75

KEY DATA		MVP 75	MVP 85	MVP 95	MVP 98
Nominal volume flow rate	m³/h	4,250			
Initial pressure drop	Pa	100	115	130	140
Class to ISO 16890		ISO ePM10 75%	ISO ePM2,5 70%	ISO ePM1 70%	ISO ePM1 85%
Particulate matter efficiency ISO ePM1 ISO ePM2,5 ISO ePM10	%	33 46 79	62 72 90	73 80 93	86 91 97
Cut-off particle size	μm	7	5	4	2.5
Filter class to EN 779:2012		M 6	F7	F8	F9
Recom. final pressure drop**	Pa		4!	50	

— MVP 85

The figures given are mean values subject to tolerances due to the normal production fluctuations. Our explicit written confirmation is always required for the correctness and applicability of the information involved in any particular case. Subject to technical alterations. You will find instructions on how to handle and dispose of loaded filters in our information on product safety and eco-compatibility.



^{*} As part of the EUROVENT Certification, rated at 3,400 m³/h

^{**}For cost-efficiency or system-specific reasons it may be appropriate to change the filters before reaching the final pressure drop stated. It can also be exceeded in certain applications.